



## Cable Lubricant LENS-10

**Field of use:**

**LENS-10** for fiber optic cable, cable and duct pre-lubrication.

**LENS 10** is particularly effective in this area due to specific additives, in order to greatly reduce the friction.

**Application:**

Shake the contents of the bottle well before use. Pre-lubricate the pipe with a small sponge, which is pressed with the help of air compresses. Then insert the cable into the pipe or into the duct.

**LENS 10** is mainly used for the lubrication of fiber optic cables in combination with the blow molding machine. However, this application depends on the type of blow molding machine and the type of machine.

**Properties:**

**LENS 10** is an emulsion of water and various polymers.

**LENS 10** is non-flammable and can work at a temperature of 0 ° C to 70 ° C be applied.

**Distribution:**

ALLTECH BOHEMIA CB a.s.  
J. Lomského 777/13  
370 06 České Budějovice 5  
www.abcb.eu  
Česká republika

**Stock:**

ALLTECH BOHEMIA CB a.s.  
Hospodářský park čp 555  
378 10 České Velenice  
sales@abcb.eu  
Česká republika

**No. 7600500**

**e 500g**